


馬達電纜

NEBM-M23G15-EH-5-Q9N-R3LEG14

料號: 5251382

★ Kernprogramm

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 基於標準 | EN 61984 |
| Cable identification | Without inscription label holder |
| 產品重量 | 1,900 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 圓形 |
| Electrical connection 1, connection type | Hybrid socket |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, connection technology | M23x1 |
| Electrical connection 1, number of pins/wires | 15 |
| Electrical connection 1, occupied pins/wires | 12 |
| Electrical connection 1, type of mounting | Screw lock |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | Plugs and cables |
| Electrical connection 2, cable outlet | 直的 |
| Electrical connection 2, connection technology | RJ45 and open end |
| Electrical connection 2, number of pins/wires | 14 |
| Electrical connection 2, occupied pins/wires | 12 |
| 工作電壓範圍 DC | 0 ... 850 V |
| 工作電壓範圍 AC | 0 ... 630 V |
| 在40°C時的可接受電流負載 | 17.8 A |
| 浪湧強度 | 6 kV |
| 電纜長度 | 5 m |
| 電纜屬性 | Suitable for energy chains |
| 電纜的測試條件 | 視需求的測試條件 |
| Bending radius, fixed cable installation | ≥ 51.2 mm |
| Bending radius, flexible cable installation | ≥ 96 mm |
| 電纜直徑 | 12.8 mm |
| 電纜直徑公差 | $\pm 0,3$ mm |
| 電纜結構 | 4x1,5(2x0,75)(2x0,24+2x2x0,15) 已屏蔽 |
| 導體的額定截面 | 1.5 mm ² 0.15 mm ² 0.24 mm ² 0.75 mm ² |
| 導線末端 | 導線末端套圈 |
| 防護等級 | IP67 |
| Note on degree of protection | 裝配狀態 |
| 環境溫度 | -40 ... 90 °C |
| Ambient temperature with flexible cable installation | -25 ... 80 °C |
| CE 符號 (參見符合的標準) | 根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| 材料備註 | 符合 RoHS 不含鹵素 |

| 特性 | 值 |
|-----------------------|--------------------------|
| 污染程度 | 3 |
| 耐腐蝕等級 CRC | 1 - Low corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| 電纜外套顏色 | 灰色 |
| Material insulation | PP |