



連接電纜

NEBV-M12G8-KD-3-M12G4

料號: 547888

FESTO

用於VPPM比例調壓閥



技術參數

特性	值
符合標準	DIN 47100 EN 61076-2-101
設計結構	Y-distributor with cables on both sides
Distributor type	1 to 2
附加功能	Distribution of the analogue inputs and outputs of a proportional pressure regulator
Cable identification	Without inscription label holder
安裝類型	With through-hole for M3 screw
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Screw lock
Electrical connection 3, function	Controller side
Electrical connection 3, design	圓形
Electrical connection 3, connection type	插頭
Electrical connection 3, cable outlet	直的
Electrical connection 3, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 3, number of pins/wires	4
Electrical connection 3, occupied pins/wires	3
Electrical connection 3, type of mounting	Screw lock
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V
在40°C時的可接受電流負載	2 A
浪湧強度	0.8 kV
Cable length 1	2.5 m
Cable length 2	0.5 m
電纜屬性	標準
Bending radius 1, fixed cable installation	>= 33 mm
Minimum bending radius with freely moveable use 1	>= 66 mm
Bending radius 2, fixed cable installation	>= 33 mm
Minimum bending radius with freely moveable use 2	>= 66 mm
Cable diameter 1	6.3 mm

特性	值
Tolerance for cable diameter 1	± 0,2 mm
Cable diameter 2	6.3 mm
Tolerance for cable diameter 2	± 0,2 mm
電纜結構	8x0,25 已屏蔽
導體的額定截面	0.25 mm ²
防護等級	IP67
Note on degree of protection	裝配狀態
環境溫度	-25 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS 不含鹵素
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Nickel-plated and gold-plated brass
Material insulation	PP