



Razdelnik NEDY-L2R1-V1-C1W4L-U-0.3L-M12G4-2.5R

Broj artikla: 8035783

FESTO



Tehnički podaci

| Svojstvo | Vrednost |
|--|---|
| Zasnovano na normi | EN 175301-803 EN 61076-2-101 |
| Konstruktivna struktura | Y-distributor with cables on both sides |
| Distributor type | 2 to 1 |
| Signal status display | LED žuti |
| Cable identification | With inscription label holder |
| Vrsta pričvršćenja | With through-hole for M2 screw sa priborom |
| Težina proizvoda | 104 g |
| Electrical connection 1, function | Controller side |
| Electrical connection 1, design | okruglo |
| Electrical connection 1, connection type | Utikači |
| Electrical connection 1, cable outlet | Ravno |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 4 |
| Electrical connection 1, occupied pins/wires | 3 |
| Electrical connection 2, function | Field device side |
| Electrical connection 2, design | ugaono |
| Electrical connection 2, connection type | 2 x utičnica |
| Electrical connection 2, cable outlet | Angled |
| Electrical connection 2, connection technology | Plug pattern type C to EN 175301-803 |
| Electrical connection 2, number of pins/wires | 4 |
| Electrical connection 2, occupied pins/wires | 2 |
| Područje pogonskog napona DC | 20,4 ... 27,6 V |
| Strujna opteretivost kod 40°C | 4 A |
| Čvrstoća na udarno naprezanje | 0,8 kV |
| Dužina kabla 1 | 2,5 m |
| Dužina kabla 2 | 0,3 m |
| Svojstvo kabla | Suitable for energy chains/robot applications |
| Uslovi ispitivanja kabla | Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Čvrstoća na torziju: > 300 000 ciklusa, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm |
| Minimum bending radius with freely moveable use 1 | 39 mm |
| Minimum bending radius with freely moveable use 2 | 39 mm |
| Prečnik kabla 1 | 3,8 mm |
| Prečnik kabla 2 | 3,8 mm |
| Nazivni presek provodnika | 0,25 mm ² |
| Mehanička zaštita | IP65 IP67 |
| Temperatura okoline | -20 ... 80 °C |
| Note on ambient temperature | -10 ... 40 °C when mounted via through-hole |
| Temperatura okoline kod pokretnog postepenja kablova | -20 ... 80 °C |
| Temperatura ležaja | -20 ... 80 °C |
| CE znak (vidi izjavu o usklađenosti) | in accordance with EU RoHS directive |

| Svojstvo | Vrednost |
|--|--|
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Materijal - napomena | RoHS komfornost Bez halogena Free of phosphoric acid ester |
| Stepen zagađenja | 3 |
| Klasa korozione otpornosti KBK | 1 - Low corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| Boja izolacije | sivo |
| Material housing | PA PC TPE-U(PUR) |
| Boja kućišta | crno |
| Material seals | NBR |
| Material electrical contact | Gold-plated copper alloy Silver-plated copper alloy |
| Material threaded sleeve | Mesing niklovan |