


Razdelnik

NEDY-L2R1-V1-Z4W2Z-U-0.3L-M8G4-5R

Broj artikla: 8035790

FESTO



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	EN 61076-2-104
Dozvola	RCM Mark
Konstruktivna struktura	Y-distributor with cables on both sides
Distributor type	2 to 1
Signal status display	LED žuti
Dodatne funkcije	Smanjenje struje držanja
Cable identification	With inscription label holder
Vrsta pričvršćenja	With through-hole for M2 screw sa priborom
Težina proizvoda	131 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	2 x utičnica
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Connection pattern ZC, metric screw
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Područje pogonskog napona DC	20,4 ... 27,6 V
Strujna opteretivost kod 40°C	1 A
Čvrstoća na udarno naprezanje	0,8 kV
Dužina kabela 1	5 m
Dužina kabela 2	0,3 m
Svojstvo kabela	Suitable for energy chains/robot applications
Note on cable characteristics	Field device side: standard
Uslovi ispitivanja kabela	Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Čvrstoća na torziju: > 300 000 ciklusa, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Note on cable test conditions	For standard cables: Energy chain: 1.5 million cycles, bending radius 75 mm, resistance to bending: to Festo standard, test conditions on request
Minimum bending radius with freely moveable use 1	39 mm
Minimum bending radius with freely moveable use 2	30 mm
Prečnik kabela 1	3,8 mm
Prečnik kabela 2	2,9 mm
Nazivni presek provodnika	0,25 mm ²
Mehanička zaštita	IP65
Temperatura okoline	-10 ... 50 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole

Svojstvo	Vrednost
Temperatura okoline kod pokretnog postopenja kablova	-5 ... 50 °C
Temperatura ležaja	-10 ... 50 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	sivo
Material housing	PA TPE-U(PUR)
Boja kućišta	crno
Material seals	NBR TPE-O
Material electrical contact	Gold-plated copper alloy Legura bakra, kalajisana
Material threaded sleeve	Mesing niklovan