



Spojni vod NEBC-R3G4-ES-1-S-R3G4-ET

Broj artikla: 8040455

FESTO



Tehnički podaci

Svojstvo	Vrednost
Cable identification	With inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	89,5 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	RJ45 as per IEC 60603-7-3
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Snap-in locking
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	RJ45 as per IEC 60603-7-3
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Snap-in locking
Područje pogonskog napona DC	0 ... 30 V
Strujna opteretivost kod 40°C	1,3 A
Čvrstoća na udarno naprezanje	0,8 kV
Note on surge resistance	Due to screening, a leakage flow of up to 20 mA is permissible.
Svojstva prenošenja	In accordance with category 5, EN 50173, class D In accordance with category 5, ISO/IEC 11801, class D
Specifikacija ethernet kabla	Tip: CAT.5
Dužina kabla	1 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Čvrstoća na izmjenično savijanje prema Festo normi, uslovi ispitivanja na zahtev Uslovi ispitivanja na zahtev Energy chain > 2 million cycles, bending radius 100 mm
Bending radius, fixed cable installation	>= 40 mm
Bending radius, flexible cable installation	>= 100 mm
Prečnik kabla	6,7 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	4 x 0.34 mm ² (star quad)
Nazivni presek provodnika	0,34 mm ²
Nominal conductor cross section (AWG)	AWG22
Mehanička zaštita	IP20
Posebne karakteristike	postojano na ulje
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-20 ... 60 °C
Temperatura ležaja	-25 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions

Svojstvo	Vrednost
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	zeleno
Material housing	Mesing niklovan PA
Boja kućišta	crno
Material electrical contact	Mesing pozlaćeno
Material insulation	PE