

# Plastično crevo PUN-H-10X1,5-TGN

Broj artikla: 8048707

FESTO

dopušteno u prehrambenom području (postojano na hidrolizu).  
Ovaj proizvod nije prikladan za utične priključke CN i PK.



## Tehnički podaci

| Svojstvo  | Vrednost   |
|---|--|
| Spoljašnji prečnik                                  | 10 mm  |
| Radius savijanja, merodavan za protok               | 52 mm  |
| Unutrašnji prečnik                                  | 7 mm   |
| Min. radius savijanja                               | 28 mm  |
| Uputstva za korišćenje                              | TPE-U Ether basiert  |
| Tubing characteristics                              | Suitable for energy chains   |
| Operating pressure for entire temperature range     | -0,095 ... 0,6 MPa   |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 6 bar  |
| Operating pressure for entire temperature range     | -13,775 ... 87 psi   |
| Temperature-dependent operating pressure            | -0,095 ... 1 MPa   |
| Pogonski pritisak zavisian od temperature           | -0,95 ... 10 bar   |
| Temperature-dependent operating pressure            | -13,775 ... 145 psi  |
| Napomena za pogonski pritisak                       | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C   |
| Dozvola   | TÜV  |
| Mesto izdavanja sertifikata                         | B 013277 0506 00   |
| Pogonski medijum                                    | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-]<br>Water (liquid, free of ice)   |
| Material fire test                                  | UL94 HB  |
| PWIS conformity                                     | VDMA24364-B2-L   |
| RSBP classification to CD-0033                      | F1a  |
| Cleanroom class                                     | This product is a static object, active particle generation is not possible when used correctly.<br>Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe   | See Supplementary material information   |
| Temperatura okoline                                 | -35 ... 60 °C  |
| Težina proizvoda prema dužini                       | 0,0465 kg/m  |
| Pneumatski priključak                               | For push-in connector outside diameter 10 mm   |
| Boja  | Translucent green  |
| Tvrdoća po Shoreu                                   | D 52 +/-3  |
| Materijal - napomena                                | RoHS komformnost   |
| Material tubing                                     | TPE-U(PU)  |