

Spojni vod NEBL-M8G4-E-5-N-LE4

Broj artikla: 8065110

FESTO



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-104
Dozvola	c UL us - Listed (OL)
Mesto izdavanja sertifikata	UL E253748
Cable identification	Without inscription label holder
Težina proizvoda	183 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hexagon A/F 9 mm and longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Područje pogonskog napona AC	0 ... 30 V
Nazivni pogonski napon AC	24 V
Strujna opteretivost kod 40°C	5,2 A
Čvrstoća na udarno naprezanje	0,8 kV
Priključak uzemljenja	ne postoji
Shielding	ne
Dužina kabla	5 m
Svojstvo kabla	Suitable for energy chains
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 15 mm
Bending radius, flexible cable installation	≥ 50 mm
Prečnik kabla	4,8 mm
Odstupanje prečnika kabla	± 0,15 mm
Struktura kabla	4x0,5
Nazivni presek provodnika	0,5 mm ²
Krajevi žica	Sheath removed Cut off bluntly
Mehanička zaštita	IP65 IP67 IP69K
Note on degree of protection	u montiranom stanju
Posebne karakteristike	postojano na ulje
Temperatura okoline	-40 ... 90 °C
Temperatura okoline kod pokretnog postepenja kablova	-20 ... 90 °C
Temperatura ležaja	-40 ... 90 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive

Svojstvo	Vrednost
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost Bez halogena
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	crno
Material housing	TPE-U(PUR)
Boja kućišta	crno
Material screw-type lock	Nickel-plated brass
Material seals	FPM
Material electrical contact	Gold-plated copper alloy
Material insulation	PP