

IO-Link Master CPX-AP-I-4IOL-M12

料號: 8086604

★ Kernprogramm

FESTO



技術參數

特性	值
通訊協定	IO-Link
尺寸 寬(W) x 長(L) x 高(H)	30 mm x 170 mm x 35 mm
安裝類型	On H-rail with accessories 具通孔
產品重量	126 g
環境溫度	-20 ... 50 °C
儲藏溫度	-40 ... 70 °C
相對空氣濕度	5 - 95 % 非冷凝
防護等級	IP65 IP67
Note on degree of protection	Unused connections sealed
耐腐蝕等級 CRC	1 - Low corrosion stress
最大行列長度	20 m with IO-Link operation 50 m system communication
PWIS conformity	VDMA24364-B2-L
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則
UKCA marking (see declaration of conformity)	To UK instructions for EMC
KC mark	KC-EMV
授權	RCM Mark c UL us - Listed (OL)
認證核發部門	UL E239998
材料備註	符合 RoHS
Material housing	PA PC Nickel-plated die-cast zinc
Material o-ring	FPM
Diagnostics via LED	Diagnostics per channel Diagnostics per module Power supply load Status per channel Status per module
Diagnostics per internal communication	IO-Link® event Short circuit/overload in sensor supply Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x 插座
Communication interface, connection technology	M8x1, D-coded to EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, screening	是
Power supply, function	Incoming electronics/sensors and load
Power supply, type of connection	插頭

特性	值
Power supply, connection technology	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	插頭插座
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
額定工作電壓, DC 輸出	24 V
Permissible voltage fluctuations, load	± 25 %
Nominal operating voltage DC for electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 55 mA
Intrinsic current consumption at nominal operating voltage load	Typical 5 mA
能源不足緩衝	10 ms
極性保護	是
Electrical connection for IO-Link®, connection type	4x 插座
Electrical connection for IO-Link®, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for IO-Link®, number of pins/wires	5
IO-Link, 通訊	C/Q 綠色 LED
IO-Link, 接口數	4
IO-Link, 接口類型	B
IO-Link, protocol	Master V 1.1
IO-Link, 通訊模式	可透過軟體配置 SIO, COM1 (4.8 kBaud), COM2 (38.4 kBaud), COM3 (230.4 kBaud)
IO-Link, process data width OUT	Can be parameterised 8 - 128 bytes
IO-Link, process data width IN	Can be parameterised 12 - 132 bytes
IO-Link, 最小周期時間	Dependent on minimum supported cycle time of the connected IO-Link® device