

Servomotor EMMT-AS-190-LK-HT-R3MYB

Broj artikla: 8148401

FESTO



Tehnički podaci

Svojstvo	Vrednost
Temperatura okoline	-15 ... 40 °C
Note on ambient temperature	up to 80°C with derating -1.5%/°C
Max. installation height	4.000 m
Note on max. installation height	As of 1,000 m, only with derating of -1.0% per 100 m
Temperatura ležaja	-20 ... 70 °C
Relativna vlažnost vazduha	0 - 90 %
Odgovara standardu	IEC 60034
Termalna klasa prema EN 60034-1	F
Max. winding temperature	155 °C
Klasa dimenzionisanja prema EN 60034-1	S1
Nadzor temperature	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM B5 IM V1 IM V3
Položaj ugradnje	proizvoljno
Mehanička zaštita	IP21
Note on degree of protection	IP21 for motor shaft without rotary shaft seal IP65 motor shaft with RWDR IP67 for motor housing with connection technology
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2,5
Detent torque	<1.0% of peak torque
Storage lifetime under nominal conditions	20.000 h
Izvedba vratila sa ravnim klinom	DIN 6885 A 10 x 8 x 45
Interface code, motor out	190B
Electrical connection 1, connection type	Hybrid plugs
Electrical connection 1, connection technology	M40x1
Electrical connection 1, number of pins/wires	15
Stepen zagađenja	2
Materijal - napomena	RoHS komfornost
Klasa korozione otpornosti KBK	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Otpornost na vibracije	prema EN 60068-2-6
Udarna čvrstoća	prema EN 60068-2-29 15 g/11 ms to EN 60068-2-27
Dozvola	c UL us - Recognized (OL)
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions
Mesto izdavanja sertifikata	TÜV 968/FSP 2317.00/21 UL E342973
Nazivni pogonski napon DC	680 V

Svojstvo	Vrednost
Vrsta spajanja navoja	Zvezda unutrašnja
Number of pole pairs	5
Obrtni moment mirovanja	93,7 Nm
Nazivni obrtni moment	82,4 Nm
Vršni obrtni moment	183,3 Nm
Nazivna brzina obrtanja	1.000 1/min
Maks. brzina obrtanja	1.654 1/min
Max. mechanical speed	8.000 1/min
Nazivna snaga motora	8.629 W
Trajna struja mirovanja	22,8 A
Nazivna struja, motor	20 A
Vršna struja	49,7 A
Motorska konstanta	4,12 Nm/A
Standstill torque constant	4,79 Nm/A
Naponska konstanta, linijska	289,7 mVmin
Otpor navoja faza-faza	0,358 Ohm
Induktivnost navoja faza-faza	13,8 mH
Winding longitudinal inductivity Ld (phase)	6,95 mH
Winding cross inductivity Lq (phase)	6,9 mH
Electric time constant	38,8 ms
Thermal time constant	80 min
Thermal resistance	0,3 K/W
Measuring flange	450 x 450 x 30, steel
Sveukupni moment inercije gonjene strane	195 kgcm ²
Težina proizvoda	61.500 g
Dozvoljeno aksijalno opterećenje vratila	520 N
Dozvoljeno radijalno opterećenje vratila	2.620 N
Senzor položaja rotora	Safety Enc. absolut multi turn
Rotor position sensor, manufacturer designation	EQI 1331
Rotor position sensor, absolute detectable revolutions	4.096
Interface rotirajućeg enkodera	EnDat 22
Princip određivanja položaja rotirajućim enkoderom	induktivno
Rotor position sensor, DC operating voltage	5 V
Rotor position sensor, DC operating voltage range	3,6 ... 14 V
Rotor position sensor, position values per revolution	524.288
Okidački enkoder rotora	19 Bit
Rotor position sensor, system accuracy of angle measurement	-65 ... 65 arcsec
Moment držanja, kočnica	115 Nm
Pogonski napon DC, kočnica	24 V
Brake current consumption	2,08 A
Primljena snaga, kočnica	50 W
Brake separation time	190 ms
Brake closing time	65 ms
DC brake response delay	12 ms
Max. brake no-load speed	8.000 1/min
Moment inercije kočnice	50 kgcm ²
Switching cycles, holding brake	5 million idle actuations (without work of friction!)
Safety Integrity Level (SIL), component parts	SIL 2, encoder
Performance Level (PL), component parts	Category 3, Performance Level d, encoder
PFHd, component parts	15 x 10E-9, encoder
Duration of use Tm, component parts	20 years, rotor position encoder
MTTF, subcomponent	190 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 1