


# Compact cylinder ADN-S-50-35-I-P

Part number: 5138184

**FESTO**



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 35 mm                                                                                      |
| Piston diameter                                              | 50 mm                                                                                      |
| Cushioning                                                   | Elastic cushioning rings/plates at both ends                                               |
| Mounting position                                            | optional                                                                                   |
| Mode of operation                                            | Double-acting                                                                              |
| Piston-rod end                                               | Female thread                                                                              |
| Design                                                       | Piston<br>Piston rod                                                                       |
| Variants                                                     | Additional PTFE piston guide                                                               |
| Operating pressure                                           | 0.04 MPa...1 MPa<br>0.4 bar...10 bar<br>5.8 psi...145 psi                                  |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 1 - Low corrosion stress                                                                   |
| LABS (PWIS) conformity                                       | VDMA24364-B2-L                                                                             |
| Cleanroom suitability, measured according to ISO 14644-14    | Class 5 according to ISO 14644-1                                                           |
| Ambient temperature                                          | 0 °C...80 °C                                                                               |
| Impact energy in end positions                               | 0.6 J                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 1057 N                                                                                     |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1178 N                                                                                     |
| Moving mass for 0 mm stroke                                  | 105 g                                                                                      |
| Additional moving mass per 10 mm stroke                      | 16 g                                                                                       |
| Basic weight for 0 mm stroke                                 | 310 g                                                                                      |
| Additional weight per 10 mm stroke                           | 63 g                                                                                       |
| Type of mounting                                             | Either:<br>With through-hole<br>Via female thread<br>With accessories                      |
| Pneumatic connection                                         | G1/8                                                                                       |
| Note on materials                                            | RoHS-compliant                                                                             |
| Material cover                                               | Anodised wrought aluminium alloy                                                           |

| Feature                | Value                            |
|------------------------|----------------------------------|
| Material dynamic seals | NBR                              |
| Material housing       | Anodised wrought aluminium alloy |
| Material piston rod    | High-alloy stainless steel       |