


接頭

NPCK-C-D-G18-K6

料號: 1366257

FESTO



技術參數

| 特性 | 值 |
|---|---|
| 額定尺寸 | 2.9 mm |
| 柱頭螺栓上的密封件類型 | 密封圈 |
| 裝配位置 | 任何 |
| 設計 | 直式結構 |
| Operating pressure for entire temperature range | -0.095 ... 1.2 MPa |
| 操作壓力的完整溫度範圍 | -0.95 ... 12 bar |
| Operating pressure for entire temperature range | -13.775 ... 174 psi |
| 操作壓力注意事項 | Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi |
| 操作介質 | 壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour |
| 注意: 操作和嚮導介質 | 潤滑操作可行 |
| 耐腐蝕等級 CRC | 4 - Very high corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| Food-safe | See Supplementary material information |
| Note on temperature of medium | Water vapour: max. 120°C |
| 防護等級 | IP69K |
| 環境溫度 | -20 ... 120 °C |
| Note on ambient temperature | The NPCK can be used from -40 to 60 °C when using suitable tubing and observing the maximum operating pressure of the tube. |
| 額定鎖緊扭矩 | 6.5 Nm |
| Note on the nominal tightening torque | 4 Nm +/-10% for NPCK to MPA-C |
| 額定擰緊扭矩公差 | ± 10 % |
| 產品重量 | 14.1 g |
| 氣壓連接, 氣口 1 | 外螺紋 G1/8 |
| 氣壓連接, 氣口 2 | For tubing outside diameter 6 mm |
| Material of union nut | 高合金鋼, 耐腐蝕 |
| Material of threaded plug | 高合金鋼, 耐腐蝕 |
| 材料備註 | 符合 RoHS |
| Material sealing ring | PEEK |