



連接電纜

NEBU-M12G5-K-2-M12W5

料號: 8003618

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 符合標準 | EN 61076-2-101 |
| Cable identification | with 2x label holders |
| 產品重量 | 77 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 圓形 |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 5 |
| Electrical connection 1, occupied pins/wires | 5 |
| Electrical connection 1, type of mounting | Screw lock |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, design | 圓形 |
| Electrical connection 2, connection type | 插頭 |
| Electrical connection 2, cable outlet | Angled |
| Electrical connection 2, connection technology | M12x1, A-coded in accordance with EN 61076-2-101 |
| Electrical connection 2, number of pins/wires | 5 |
| Electrical connection 2, occupied pins/wires | 5 |
| Electrical connection 2, type of mounting | Screw lock |
| 工作電壓範圍 DC | 0 ... 60 V |
| 工作電壓範圍 AC | 0 ... 60 V |
| 在40°C時的可接受電流負載 | 4 A |
| 浪湧強度 | 1.5 kV |
| 電纜長度 | 2 m |
| 電纜屬性 | 標準 |
| 電纜的測試條件 | 彎折強度符合 Festo 標準, 測試條件根據需求 視需求的測試條件 Energy chain: > 5 million cycles, bending radius 75 mm |
| Bending radius, fixed cable installation | 14 mm |
| Bending radius, flexible cable installation | 46 mm |
| 電纜直徑 | 4.5 mm |
| 電纜直徑公差 | ± 0,1 mm |
| 電纜結構 | 5x0,25 |
| 導體的額定截面 | 0.25 mm ² |
| 防護等級 | IP65 IP68 IP69K |
| Note on degree of protection | 裝配狀態 |
| Special characteristics | 耐油 |
| 環境溫度 | -25 ... 70 °C |
| Ambient temperature with flexible cable installation | -5 ... 70 °C |
| CE 符號 (參見符合的標準) | 根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |

| 特性 | 值 |
|-----------------------------|--|
| 材料備註 | 符合 RoHS 不含鹵素 Free of phosphoric acid ester |
| 污染程度 | 3 |
| 耐腐蝕等級 CRC | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| 電纜外套顏色 | 灰色 |
| Material housing | TPE-U(PUR) |
| 外殼顏色 | 黑色 |
| Material screw-type lock | Nickel-plated brass |
| Material seals | NBR |
| Material electrical contact | Gold-plated copper alloy |
| Material insulation | PP |