


# linear gantry YXCL-2

料號: 8024300

FESTO



## 技術參數

| 特性   | 值   |
|--|---|
| Required flatness of the mounting surfaces | 0.1 mm/m  |
| 裝配位置                                       | 水平  |
| 設計結構                                       | Linear gantry system<br>With electric and pneumatic drive modules |
| 循環功率                                       | 100 %   |
| PWIS conformity                            | VDMA24364 zone III  |
| 儲藏溫度                                       | -20 ... 60 °C   |
| 相對空氣濕度                                     | 0 - 90 %  |
| 環境溫度                                       | 5 ... 45 °C   |
| Maintenance interval                       | 2,500 km  |
| 材料備註                                       | 符合 RoHS   |
| Material adapter plate                     | Anodised aluminium<br>Coated steel                                |
| Material mounting bracket                  | 高合金鋼, 耐腐蝕   |
| Material energy chains                     | PA-加強   |