


Valve terminal VTUX-A-S-APA-

Part number: 8000815

FESTO



Data sheet

Feature	Value
Grid dimension	10.55 mm...12.55 mm
Type of mounting	Tie rod
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
Max. installation height	3500 m
Degree of protection	IP20 IP40 IP65
Corrosion resistance class CRC	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Continuous shock resistance to DIN/IEC 68 Part 2-82	Tested according to severity level 1
Operating pressure	-0.1 MPa...0.7 MPa -1 bar...7 bar
Pilot pressure	0.15 MPa...0.7 MPa 1.5 bar...7 bar
Operating pressure for valve terminal with internal pilot air supply	1.5 bar...7 bar
LABS (PWIS) conformity	VDMA24364-C1-L
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
Approval	RCM trademark
Note on materials	RoHS-compliant
Valve terminal structure	Modular and expandable
Max. number of valve positions	64
Max. number of pressure zones	16
Type of actuation	Electric
Valve function	2x3/2-way, monostable, closed 2x3/2-way, open, monostable 5/2 double solenoid 5/2-way, monostable 5/3 closed

Feature	Value
Design	Piston gate valve
Sealing principle	Soft
Type of piloting	Pilot actuated
Pilot air supply	External Internal
Nominal flow rate standardised according to ISO 8778	470 l/min...690 l/min
Suitability for vacuum	yes
Exhaust-air function	With flow control option
Pneumatic connection, port 1	QS-8 QS-10 QS-12 QS-5/16 QS-3/8 For 15 mm cartridge Blanking plug
Pneumatic connection, port 2	QS-4 QS-6 QS-8 QS-5/32 QS-1/8 QS-1/4 QS-5/16 For 10 mm cartridge For 12 mm cartridge Blanking plug
Pneumatic connection, port 3	QS-8 QS-10 QS-12 QS-5/16 QS-3/8 For 15 mm cartridge Silencer Blanking plug
Pneumatic connection, port 4	QS-4 QS-6 QS-8 QS-5/32 QS-1/8 QS-1/4 QS-5/16 For 10 mm cartridge For 12 mm cartridge Blanking plug
Pneumatic connection, port 5	QS-8 QS-10 QS-12 QS-5/16 QS-3/8 Silencer For 15 mm cartridge Blanking plug
Pilot air port 12/14	Blanking plug QS-4 QS-6 QS-8 QS-5/16 QS-1/4 For 12 mm cartridge
Pilot exhaust port 82/84	QS-4 QS-6 QS-8 QS-5/16 QS-1/4 Silencer For 12 mm cartridge
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %