

# 塑料氣管

## PAN-R-22X2-SW

料號: 8036207

FESTO



### 技術參數

特性	值
外徑	22 mm
與流量相關的彎曲半徑	350 mm
內徑	18 mm
Operating pressure for entire temperature range 操作壓力的完整溫度範圍	-0.095 ... 0.8 MPa -0.95 ... 8 bar
Operating pressure for entire temperature range 溫度取決於操作壓力	-13.775 ... 116 psi -0.095 ... 1.4 MPa -0.95 ... 14 bar
Temperature-dependent operating pressure 溫度取決於操作壓力	-13.775 ... 203 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
環境溫度	-30 ... 80 °C
產品重量視長度而定	0.131 kg/m
氣壓連接	For push-in connector outside diameter 22 mm
顏色	黑色
肖氏硬度	D 62 +/-3
材料備註	符合 RoHS
Material tubing	TPE-A