



## 連接電纜

### NEBB-M12W5-P-10-LE5

料號: 8066687

FESTO



## 技術參數

| 特性   | 值  |
|--|--|
| 符合標準   | Core colours and connection numbers to EN 60947-5-2<br>EN 61076-2-101  |
| Cable identification                           | With inscription label holder  |
| Electrical connection 1, function              | Field device side  |
| Electrical connection 1, design                | 圓形   |
| Electrical connection 1, connection type       | 插頭插座   |
| Electrical connection 1, cable outlet          | Angled   |
| Electrical connection 1, connection technology | M12x1, A-coded in accordance with EN 61076-2-101                       |
| Electrical connection 1, number of pins/wires  | 5  |
| Electrical connection 1, occupied pins/wires   | 5  |
| Electrical connection 1, type of mounting      | Screw lock with A/F13  |
| Electrical connection 2, function              | Controller side  |
| Electrical connection 2, connection type       | 電纜   |
| Electrical connection 2, connection technology | 開放式終端  |
| Electrical connection 2, number of pins/wires  | 5  |
| Electrical connection 2, occupied pins/wires   | 5  |
| 工作電壓範圍 DC                                      | 0 ... 60 V   |
| 工作電壓範圍 AC                                      | 0 ... 60 V   |
| 在40°C時的可接受電流負載                                 | 4 A  |
| 浪湧強度   | 1.5 kV   |
| 電纜長度   | 10 m   |
| 電纜屬性   | 用於靜態應用   |
| 電纜的測試條件  | 視需求的測試條件   |
| Bending radius, fixed cable installation       | >= 14 mm   |
| 電纜直徑   | 4.5 mm   |
| 電纜結構   | 5x0,25   |
| 導體的額定截面  | 0.25 mm <sup>2</sup>   |
| 導線末端   | Sheath removed<br>Cut off bluntly                                      |
| 防護等級   | IP65<br>IP68<br>IP69K  |
| Note on degree of protection                   | 裝配狀態   |
| 環境溫度   | -25 ... 70 °C  |
| CE 符號 (參見符合的標準)                                | 根據 EU 低電壓設備指導原則<br>in accordance with EU RoHS directive                |
| UKCA marking (see declaration of conformity)   | To UK instructions for electrical equipment<br>To UK RoHS instructions |
| PWIS conformity                                | VDMA24364-B2-L   |
| 無塵室等級  | ISO class 4  |
| 材料備註   | 符合 RoHS  |
| 污染程度   | 3  |
| 耐腐蝕等級 CRC                                      | 2 - Moderate corrosion stress  |
| Material cable sheath                          | PVC  |
| 電纜外套顏色   | 灰色   |
| Material housing                               | TPE-U(PU)  |

| 特性                          | 值                        |
|-----------------------------|--------------------------|
| 外殼顏色                        | 黑色                       |
| Material screw-type lock    | Nickel-plated brass      |
| Material seals              | NBR                      |
| Material electrical contact | Gold-plated copper alloy |
| Material insulation         | PVC                      |