

螺桿軸

ELGT-BS-160-650-10P

料號: 8124520

FESTO



技術參數

特性	值
工作行程	650 mm
尺寸	160
備用行程	0 mm
反向空隙	$\leq 0.15 \mu\text{m}$
螺桿直徑	20 mm
螺桿螺距	10 mm/U
裝配位置	任何
導向	迴圈滾珠軸承導向
設計結構	機電式直線軸 具迴圈滾珠軸承螺桿
馬達類型	步進馬達 伺服馬達
螺桿類型	滾珠螺紋螺桿
多樣型	Recommended for production facilities for the manufacture of lithium-ion batteries
最大加速度	15 m/s ²
最高速度	3,000 1/min 0.5 m/s
重複精度	$\pm 0.02 \text{ mm}$
循環功率	100 %
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
無塵室等級	ISO class 8
防護等級	IP20
環境溫度	0 ... 50 °C
固定的輸送力	1,575 N
轉動面積矩 2nd 度ly	1,411E+03 mm ⁴
轉動面積矩 2nd 度lz	15,257E+03 mm ⁴
No-load torque at maximum travel speed	0.4 Nm
No-load torque at minimum travel speed	0.2 Nm
最大輸出力Fy	9,550 N
最大輸出力Fz	11,370 N
Fy with theoretical service life of 100 km (from a guide perspective only)	35,183 N
Fz with theoretical service life of 100 km (from a guide perspective only)	41,887 N
最大扭矩Mx	600 Nm
最大扭矩My	560 Nm
最大扭矩Mz	560 Nm
Mx with theoretical service life of 100 km (from a guide perspective only)	2,210 Nm
My with theoretical service life of 100 km (from a guide perspective only)	2,063 Nm
Mz with theoretical service life of 100 km (from a guide perspective only)	2,063 Nm
驅動軸的最大徑向力	340 N

特性	值
最大進給力 Fx	1,575 N
質量慣性扭矩	726E+03 mm ⁴
每公尺行程的質量慣性力矩 JH	809 kgcm ²
每kg工作負荷的質量慣性力矩 JL	0.0253 kgcm ²
質量慣性力矩, JO	0.3175 kgcm ²
恆定進給	10 mm/U
運動質量	3,855 g
產品重量	21,755 g
0 mm行程時的基本重量	9,564 g
每 10 mm 行程所增加的重量	188 g
Dynamic deflection (load moved)	0.05% of the axis length, max. 0.5 mm
Static deflection (load at standstill)	0.1% of the axis length
Interface code, actuator	T46
Material of end caps	Die-cast aluminium, painted
Material of profile	Anodised wrought aluminium alloy
材料備註	符合 RoHS
Material drive cover	Die-cast aluminium, painted
Material guide slide	鋼
Material guide rail	鋼
Material slide	Anodised wrought aluminium alloy
Material spindle nut	鋼
Material spindle	鋼