


Stepper motor EMMB-ST-87-S-SB

Part number: 8156152

FESTO



Data sheet

| Feature | Value |
|--|--|
| Ambient temperature | -15 °C...40 °C |
| Note on ambient temperature | Up to 80°C with derating -2%/°C |
| Max. installation height | 4000 m |
| Note on max. installation height | As of 1,000 m: only with derating of -1.0% per 100 m |
| Storage temperature | -20 °C...70 °C |
| Relative air humidity | 0 - 90% |
| Conforms to standard | IEC 60034 |
| Temperature class as per EN 60034-1 | B |
| Max. winding temperature | 130 °C |
| Rating class as per EN 60034-1 | S1 |
| Motor type to EN 60034-7 | IM B5 IM V1 IM V3 |
| Mounting position | optional |
| Degree of protection | IP20 |
| Note on degree of protection | IP40 for motor shaft without rotary shaft seal |
| Interface code, motor out | 87A |
| Electrical connection 1, connection type | Hybrid plug |
| Electrical connection 1, connector system | Plug pattern L10 |
| Electrical connection 1, number of connections/cores | 14 |
| Note on materials | RoHS-compliant |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Vibration resistance | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27 |
| Approval | RCM trademark |
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| CE marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Nominal operating voltage DC | 48 V |
| Number of pole pairs | 50 |

| Feature | Value |
|---|---|
| Motor holding torque | 2.4 Nm |
| Peak torque | 2.7 Nm |
| Max. rotational speed | 2200 rpm |
| Max. mechanical speed | 8000 rpm |
| Stepper angle for complete step | 1.8 deg |
| Stepping angle tolerance | ±5% |
| Continuous stall current | 9.5 A |
| Nominal motor current | 6.9 A |
| Peak current | 12 A |
| Motor constant | 0.24 Nm/A |
| Voltage constant, phase | 15.4 mV/min |
| Phase winding resistance | 0.13 Ohm |
| Phase winding inductance | 0.35 mH |
| Winding longitudinal inductivity Ld (phase) | 0.56 mH |
| Winding cross inductivity Lq (phase) | 0.35 mH |
| Electric time constant | 1.75 ms |
| Thermal time constant | 37 min |
| Thermal resistance | 0.91 K/W |
| Measuring flange | 250 x 250 x 15 mm, steel |
| Total mass moment of inertia of output | 1.11 kgcm ² |
| Product weight | 2720 g |
| Permissible axial shaft load | 60 N |
| Permissible radial shaft load | 220 N |
| Brake holding torque | 4.26 Nm |
| Operating voltage DC for brake | 24 V |
| Brake current consumption | 0.49 A |
| Power consumption, brake | 12 W |
| Brake coil resistance | 49.2 Ohm |
| Brake coil inductivity | 110 mH |
| Brake separation time | 44 ms |
| Brake closing time | 110 ms |
| DC brake response delay | 30 ms |
| Max. brake no-load speed | 7000 rpm |
| Max. friction per braking process | 14000 J |
| Mass moment of inertia of brake | 0.11 kgcm ² |
| Switching cycles holding brake | 10 million idle actuations (without friction work!) |