


system supply CPX-AP-A-S-1-PP-5P

料號: 8129253

FESTO



技術參數

| 特性 | 值 |
|-------------------------------------|---|
| 尺寸 寬(W) x 長(L) x 高(H) | (installation dimensions) 50,1 mm x 153 mm x 45,6 mm |
| 網柵尺寸 | 50.1 mm |
| 安裝類型 | On H-rail with accessories With through-hole for M5 screw with accessories With through-hole for M6 screw with accessories |
| 產品重量 | 182 g |
| 裝配位置 | Any, on H-rail: horizontal |
| 環境溫度 | -20 ... 50 °C |
| Note on ambient temperature | Note ambient temperature derating according to IEC 61131-2:2017 |
| 儲藏溫度 | -20 ... 70 °C |
| 相對空氣濕度 | 5 - 95 % 非冷凝 |
| Nominal altitude of use | <= 2000 m ASL (> 79,5 kPa) |
| Max. installation height | 3,500 m |
| Note on max. installation height | > 2000 m ASL (< 79,5 kPa) Note ambient temperature derating according to IEC 61131-2:2017 |
| 耐腐蝕等級 CRC | 1 - Low corrosion stress |
| 耐振動 | 傳送應用測試在安全等級 2 符合 FN 942017-4 及 EN 60068-2-6 |
| Note on vibration resistance | SG1 on H-rail SG2 on direct mounting 傳送應用測試在安全等級 1 符合 FN 942017-4 及 EN 60068-2-6 |
| 耐衝擊 | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Note on shock resistance | 30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27 |
| 安全等級 | III |
| Overvoltage category | II |
| PWIS conformity | VDMA24364-B2-L |
| Material fire test | UL94 V-0 (housing) |
| 材料備註 | 符合 RoHS 不含鹵素 Free of phosphoric acid ester |
| Material housing | PA-加強 |
| Material flange | Nickel-plated die-cast zinc |
| Material screws | Steel, nickel-plated |
| Material seals | PU 泡沫 |
| Power supply, function | Incoming electronics/sensors and load and functional earth |
| Power supply, type of connection | 插頭 |
| Power supply, connection technology | Push-pull according to IEC 61076-3-126 |
| Power supply, number of pins/wires | 5 |
| Note regarding operating voltage | SELV/PELV fixed power supplies required Note voltage drop |

| 特性 | 値 |
|--|--|
| Note on nominal operating voltage DC | 2x24 V [XD1,PS,PL] Prot.Ext.Low-Volt. IEC 60204-1 |
| 額定工作電壓, DC 輸出 | 24 V |
| Nominal operating voltage DC for electronics/sensors | 24 V |
| Power supply, conductor diameter | 2.5 mm ² |
| 額定電流 | 10 A |
| Max. power supply | 2 x 10 A (external fuse required) |
| Potential separation between the supply voltages electronics/sensors and load/valves | 是 |