



代表範例

技術參數

整體數據表 – 個別數值取決於您的配置。

特性	值
Operating pressure MPa	0 ... 0.9 MPa
操作壓力	0 ... 9 bar
Operating pressure	0 ... 130.5 psi
尺寸	100 mm
多樣型	Manifold block for safety functions, HFT0 prepared for exhausting, VDI/VDE 3845 Manifold block for safety functions, HFT0 prepared for exhausting, VDI/VDE 3847 Manifold block for safety functions, HFT1 prepared for exhausting, VDI/VDE 3847 End plate, double-acting, effective direction can be switched Filter regulator, pressure range 0.5 ... 12 bar, grade of filtration 40 µm Filter regulator, pressure range 0.5 ... 12 bar, grade of filtration 5 µm Module for reaching a defined end position in the event of a pressure failure Volume booster, double-acting Volume booster, single-acting
裝配位置	任何
操作介質	壓縮空氣符合 ISO8573-1:2010 [-:7:-] 惰性氣體
注意: 操作和嚮導介質	潤滑操作不可行
耐振動	Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
耐衝擊	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27
Note on shock resistance	With more than 3 modules, additional mounting requirements are necessary or values are reduced Valid for max. 3 modules + end plate
耐腐蝕等級 CRC	3 - High corrosion stress
PWIS conformity	VDMA24364 zone III
安裝類型	具配件
氣壓連接	Sub-base design, airing
Material housing	Smooth-anodised wrought aluminium alloy (20 µm)
Material cover	Smooth-anodised wrought aluminium alloy (20 µm)
Material screws	高合金鋼, 耐腐蝕
Material spring	彈簧鋼
Material seals	EPDM NBR
Material rotary knob	POM
Material filter	PE
材料備註	符合 RoHS