

# Compact cylinder ADN-S-40-20-A-P

Part number: 8092068

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 20 mm  |
| Piston diameter  | 40 mm  |
| Cushioning   | Elastic cushioning rings/plates at both ends   |
| Mounting position  | optional   |
| Mode of operation  | Double-acting  |
| Piston-rod end   | Male thread  |
| Design   | Piston<br>Piston rod   |
| Variants   | Additional PTFE piston guide   |
| Operating pressure   | 0.06 MPa...1 MPa<br>0.6 bar...10 bar<br>8.7 psi...145 psi                                  |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                       | VDMA24364-B2-L   |
| Cleanroom suitability, measured according to ISO 14644-14    | Class 5 according to ISO 14644-1   |
| Ambient temperature  | 0 °C...80 °C   |
| Impact energy in end positions                               | 0.36 J   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 686 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 754 N  |
| Moving mass for 0 mm stroke                                  | 56 g   |
| Additional moving mass per 10 mm stroke                      | 9 g  |
| Basic weight for 0 mm stroke                                 | 186 g  |
| Additional weight per 10 mm stroke                           | 45 g   |
| Type of mounting   | Either:<br>With through-hole<br>Via female thread<br>With accessories                      |
| Pneumatic connection   | G1/8   |
| Note on materials  | RoHS-compliant   |
| Material cover   | Anodised wrought aluminium alloy   |

| <b>Feature</b>         | <b>Value</b>                     |
|------------------------|----------------------------------|
| Material dynamic seals | NBR                              |
| Material housing       | Anodised wrought aluminium alloy |
| Material piston rod    | High-alloy stainless steel       |