


Position transmitter SDAC-MHS-M20-1L-V-E-2.5-LE

Part number: 8128403

FESTO



Data sheet

Feature	Value
Design	For C-slot
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant Free of halogen
Instructions on use	Support / actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Magnetic Hall
Sensing range	25 mm
Ambient temperature	-40 °C...80 °C
Typical sampling interval	2 ms
Max. travel speed	4 m/s
Displacement resolution	0.047 mm
Repetition accuracy	0.2 mm
Analogue output	0 - 10 V
Sensitivity	0.45 V/mm
Typical linearity error	±2 mm
Min. load resistance voltage output	10 kOhm
Short circuit current rating	yes
Overload protection	Available
Output signal	Analogue
Operational voltage range DC	15 V...30 V
Residual ripple	10%
No-load supply current	12 mA
Reverse polarity protection	yes
Electrical connection 1, connection type	Cable
Electrical connection 1, connector system	Open end
Electrical connection 1, number of connections/cores	3
Connection outlet orientation	In-line

Feature	Value
Test conditions cable	Bending strength: to Festo standard Torsionsfestigkeit: > 300 000 Zyklen, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Cable length	2.5 m
Cable characteristic	Suitable for energy chains/robot applications
Cable sheath colour	Grey
Material cable sheath	TPE-U(PUR)
Type of mounting	Screw-clamped Insertable in the slot lengthwise
Mounting position	optional
Product weight	21 g
Material housing	PA-reinforced High-alloy stainless steel
Status indication	LED red, green
Ambient temperature with moving cable	-20 °C...70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1