


Ball valve unit VZBA-A-3/4-GG-63-T-22-F0304-V4V4T-PA20

Part number: 8191804

FESTO



Data sheet

Feature	Value
Design	2-way ball valve Semi-rotary drive
Type of actuation	Pneumatic
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	Rp3/4
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F0304
Nominal size DN	20
Valve function	2/2
Flow direction	Reversible
Operating pressure	0.55 MPa...0.8 MPa 5.5 bar...8 bar 79.75 psi...116 psi
Nominal pressure PN	63
Breakaway torque at differential pressure, nominal pressure, process valve PN	14 Nm
Based on standard	DIN 3202-M3 EN 10226-1 ISO 5211
Medium	Compressed air to ISO 8573-1:2010 [-:~:] Inert gases Water – no water vapour Neutral fluids Other media on request
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Media temperature	-10 °C...200 °C
Flow rate Kv	45.6 m³/h
Max. surface temperature assembly	+105 °C...+280 °C T4...T2

Feature	Value
explosion group assembly	IIC, IIIC
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	High-alloy stainless steel
Material number housing	1.4408
Material seat seal	PTFE
Material seals	PTFE reinforced
Material ball	High-alloy stainless steel
Material number ball	1.4408
Material shaft	High-alloy stainless steel
Material number shaft	1.4401
Product weight	2300 g
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Explosion ambient temperature	-10 °C ≤ Ta ≤ +80 °C
Corrosion resistance class CRC	1 - Low corrosion stress