


Adapter plate VABA-C13-G14

Part number: 8194539

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	Adapter for remote application
Operating pressure	0 MPa...0.8 MPa 0 bar...8 bar
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:7:-] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Media temperature	-40 °C...80 °C
Ambient temperature	-40 °C...80 °C
Product weight	222 g
Type of mounting	With accessories
Pneumatic connection	Sub-base design, airing
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 4	G1/4
Note on materials	RoHS-compliant
Material cover	Smooth-anodised wrought aluminium alloy (20 µm)
Material seals	EPDM NBR
Material housing	Smooth-anodised wrought aluminium alloy (20 µm)
Material screws	High-alloy stainless steel