

# Guided drive DGRC-GF-32-100-PA

Part number: 8218218

FESTO



## Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	100 mm
Piston diameter	32 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.15 MPa...1 MPa 1.5 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production according to the Festo internal definition of the degree of severity F1A with restrictions regarding the use of Cu/Zn/Ni
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.4 Nm
Max. force Fy	989.7 N
Max. force Fy static	989.7 N
Max. force Fz	989.7 N
Max. force Fz static	989.7 N
Max. moment Mx	37.61 Nm
Max. torque Mx static	37.61 Nm
Max. moment My	29.19 Nm
Max. torque My static	29.19 Nm

<b>Feature</b>	<b>Value</b>
Max. moment Mz	29.19 Nm
Max. torque Mz static	29.19 Nm
Max. permissible torque load Mx as a function of stroke	6.17 Nm
Max. effective load dependent upon stroke at defined distance xs	126.3 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	415 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	482 N
Torsional backlash	0.045 deg
Moving mass	768.8 g
Product weight	1565 g
Basic weight for 0 mm stroke	796.2 g
Centre of gravity of moving mass as a function of stroke	72.9 mm
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material guide rod	High-alloy steel
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy steel