


Motor cable

NEBM-H17G12-FH-10-Q9N-R3LEG14

Part number: 8226145

FESTO



Data sheet

Feature	Value
Based on standard	EN 61984
Cable designation	Without inscription label holder
Product weight	2.23 kg
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M21x1
Electrical connection 1, number of connections/cores	12
Electrical connection 1, used connections/cores	12
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	RJ45 and open end
Electrical connection 2, number of connections/cores	14
Electrical connection 2, used connections/cores	12
electrical connection 2, type of mounting	Plug-in
Operational voltage range DC	0 V...850 V
Operational voltage range AC	0 V...630 V
Current rating at 40° C	17.8 A
Immunity to surge	6 kV
Shielding	yes
Cable length	10 m
Cable characteristic	Suitable for use in the food industry
Test conditions cable	Test conditions on request
Bending radius, fixed cable	57.5 mm
Cable diameter	11.5 mm
Cable diameter tolerance	± 0.3 mm
Cable structure	$4 \times 1.5 \text{ mm}^2 + 1 \times (2 \times 0.75 \text{ mm}^2) + 1 \times (2 \times 0.24 \text{ mm}^2 + 2 \times 2 \times 0.15 \text{ mm}^2)$

Feature	Value
Nominal cross section conductor	0.15 mm ² 0.24 mm ² 0.75 mm ² 1.5 mm ²
Wire ends	Wire ferrule
Degree of protection	IP20 IP69K
Note on degree of protection	In assembled state
Ambient temperature	-40 °C...90 °C
Ambient temperature with moving cable	-25 °C...80 °C
Overvoltage category	III
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen
Pollution degree	3
Corrosion resistance class CRC	4 - Very high corrosion stress
Material cable sheath	TPE-E
Cable sheath colour	Grey
Material insulating sheath	PP