

Manifold sub-base for vacuum VABX-A-P-VP-BH-VH

FESTO

Part number: 8227840



Data sheet

Feature	Value
Construction width	12.5 mm
Width	12.55 mm
Length	127.6 mm
Grid dimension	12.55 mm
Valve size	10 mm
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Silencer design	Open
Type of actuation	Electric
Reverse polarity protection	yes
Sealing principle	Soft
Mounting position	optional
Adjustment component	Slotted head screw
Max. number of valve positions	1
Grade of filtration	40 µm
Integrated function	Electric ejector pulse Electric ejector pulse valve Flow control Electric on-off valve Filter With electrical interlinking module
Type of piloting	Pilot actuated
Pilot air supply	Internal
Valve function	5/3-way, pressurised 1 to 2, 4 to 5 closed
Max. number of valve coils	2
Compatible with	Valve terminal VTUX-A-P
Display type	LED
Signal status display	Yellow LED, valve control
Operating pressure	0.2 MPa...0.7 MPa 2 bar...7 bar
Nominal operating pressure	0.6 MPa 6 bar 87 psi

Feature	Value
Pilot pressure	0.2 MPa...0.7 MPa 2 bar...7 bar
Dimensions (W x L x H)	12.55 mm x 127.6 mm x 68.8 mm
Inductive protective circuit	Integrated
Nominal operating voltage DC of load	24 V
Nominal operating voltage DC	24 V
Permissible voltage fluctuation of load	± 10%
Permissible voltage fluctuations	+/- 10 %
Approval	RCM trademark
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Ester oil < 0.1mg/m ³ , according to ISO 8573-1:2010 [-::2] Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95%
Degree of protection	IP65
Note on degree of protection	In assembled state
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:-]
Ambient temperature	-5 °C...50 °C
Nominal altitude of use	<= 2000 m NHN
Max. installation height	2000 m
Product weight	52.7 g
Electrical control	Multi-pin plug
Type of mounting	Tie rod
Pneumatic connection, port 2	QS-4 QS-6 QS-8 QS-5/32 QS-1/8 QS-1/4 QS-5/16 For tubing outside diameter of 4 mm For tubing outside diameter of 6 mm For tubing outside diameter of 8 mm For tubing outside diameter of 5/32" For tubing outside diameter of 1/4" For tubing outside diameter of 5/16"
Note on materials	RoHS-compliant
Material sub-base	PA-reinforced
Material seals	HNBR NBR
Material filter	Fabric PA PE POM
Material foil	Polyester
Material housing	PA-reinforced
Material sleeve	Reinforced PA
Material clip	High-alloy stainless steel
Material nut	High-alloy stainless steel
Material o-ring	HNBR NBR
Material adjusting screw	PA-reinforced

Feature	Value
Material screws	High-alloy stainless steel