


Manifold sub-base for vacuum VABX-A-S-VE-BH-VB07H

FESTO

Part number: 8233482



Data sheet

Feature	Value
Construction width	12.5 mm
Width	12.55 mm
Length	150.8 mm
Nominal size, Laval nozzle	0.7 mm
Grid dimension	12.55 mm
Valve size	10 mm
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Silencer design	Open
Type of actuation	Electric
Reverse polarity protection	yes
Sealing principle	Soft
Mounting position	optional
Ejector characteristic	High vacuum
Adjustment component	Slotted head screw
Diagnostics per internal communication	Load switch-off Electronics/sensors overvoltage Electronics/sensors undervoltage
Max. number of valve positions	1
Integrated function	Electric ejector pulse Electric ejector pulse valve Flow control Pressure sensor Pressure transmitter Electric on-off valve Air saving function, electrical Check valve Open silencer With electrical interlinking module
Type of piloting	Pilot actuated
Pilot air supply	Internal
Valve function	2x3/2-way, monostable, closed
Max. number of valve coils	2
Display type	LED

Feature	Value
Signal status display	yes
Operating pressure for max. suction flow rate	3 bar
Operating pressure	0.2 MPa...0.7 MPa 2 bar...7 bar
Operating pressure for max. vacuum	4.4 bar
Nominal operating pressure	0.6 MPa 87 psi
Pilot pressure	0.2 MPa...0.7 MPa 2 bar...7 bar
Max. suction flow rate against atmosphere	18 l/min
Air supply time at nominal operating pressure	0.37 s
Dimensions (W x L x H)	12.55 mm x 150.8 mm x 68.8 mm
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typical 27 mA
Intrinsic current consumption at nominal operating voltage load	Typical 2.5 mA
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Power consumption at 24VDC	0.65 W
Nominal DC operating voltage, electronics/sensors	24 V
Nominal operating voltage DC of load	24 V
Power failure bridging	10 ms
Electrical isolation of outputs between channel - internal communication	yes
Potential separation between the supply voltages electronics/sensor technology and load/valves	Yes
Permissible voltage fluctuations for electronics/sensors	±10%
Permissible voltage fluctuation of load	± 10%
Approval	RCM trademark
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Ester oil < 0.1mg/m³, according to ISO 8573-1:2010 [:::2] Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95%
Degree of protection	IP65
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:-]
Ambient temperature	-5 °C...50 °C
Nominal altitude of use	<= 2000 m NHN
Max. installation height	2000 m
Product weight	68 g
Pressure measuring range	-1 bar...1 bar
Electrical control	AP interface
Communication interface, protocol	AP-COM
Type of mounting	Tie rod

Feature	Value
Pneumatic connection, port 2	QS-4 QS-6 QS-8 QS-5/32 QS-1/8 QS-1/4 QS-5/16 For tubing outside diameter of 4 mm For tubing outside diameter of 6 mm For tubing outside diameter of 8 mm For tubing outside diameter of 5/32" For tubing outside diameter of 1/4" For tubing outside diameter of 5/16"
Note on materials	RoHS-compliant
Material receiver nozzle	POM
Material o-ring	HNBR NBR
Material silencer	PP PU foam
Material transmitter nozzle	Wrought aluminium alloy