


Position transmitter SDAC-MHS-M20-1L-V-E-2.5-LE

Part number: 8128403

FESTO



Data sheet

Feature	Value
Design	for round slot
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant Halogen-free
Application note	Support / actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Magnetic Hall
Sensing range	25 mm
Ambient temperature	-40 °C...80 °C
Typical sampling interval	2 ms
Max. travel speed	4 m/s
Displacement resolution	0.047 mm
Repetition accuracy	0.2 mm
Analog output	0 - 10 V
Sensitivity	0.45 V/mm
Typical linearity error	±2 mm
Min. load resistance of voltage output	10 kOhm
Short-circuit protection	yes
Overload protection	Available
Output signal	Analog
DC operating voltage range	15 V...30 V
Residual ripple	10%
Idle current	12 mA
Reverse polarity protection	yes
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connection outlet orientation	Longitudinal

Feature	Value
Connector cable test conditions	Flexural strength: as per Festo standard Torsionsfestigkeit: > 300 000 Zyklen, ±270°/0,1 m Energy chain > 5 million cycles, bending radius 28 mm
Cable length	2.5 m
Cable characteristic	Suitable for energy chains/robot applications
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)
Type of mounting	Screwed tightly Can be inserted in slot lengthwise
Mounting position	Any
Product weight	21 g
Housing material	PA-reinforced High-alloy stainless steel
Status indicator	LED red, green
Ambient temperature with flexible cable installation	-20 °C...70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1