


Position transmitter

SDAC-MHS-M30-1L-PNLK-PN-E-0.3-M8

Part number: 8128404

FESTO



Data sheet

Feature	Value
Design	for round slot
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant Halogen-free
Application note	Support / actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Magnetic Hall
Sensing range	35 mm
Ambient temperature	-40 °C...80 °C
Typical sampling interval	2 ms
Max. travel speed	4 m/s
Displacement resolution	0.012 mm
Repetition accuracy	0.2 mm
Switching output	2x PNP or 2x NPN adjustable
Switching element function	N/C contact/N/O contact switchable
On time	3 ms
Switch-off time	3 ms
Max. switching frequency	166 Hz
Max. switching output voltage DC	30 V
Max. output current	50 mA
Max. switching capacity DC	1.5 W
Voltage drop	0.4 V
Typical linearity error	±2 mm
Short-circuit protection	yes
Overload protection	Available
Protocol	IO-Link®
IO-Link, revision ID	V1.1

Feature	Value
IO-Link, device profile	Function Locator Identification and diagnosis Measuring and Switching Sensor Smart Sensor - SSP 4.1.1
IO-Link, transmission rate	COM2
IO-Link®, SIO mode support	Yes
IO-Link, port type	Class A
IO-Link, process data length input	32 bit
IO-Link®, process data content IN	Position value 16-bit MDC Monitoring 4-bit SSC
IO-Link®, minimum cycle time	3 ms
DC operating voltage range	10 V...30 V
Residual ripple	10%
Idle current	19 mA
Reverse polarity protection	yes
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hexagon AF 9 and longitudinal knurl
Connection outlet orientation	Longitudinal
Material of pin contacts	Brass, nickel-plated and gold-plated
Connector cable test conditions	Flexural strength: as per Festo standard Torsionsfestigkeit: > 300 000 Zyklen, ±270°/0,1 m Energy chain > 5 million cycles, bending radius 28 mm
Cable length	0.3 m
Cable characteristic	Suitable for energy chains/robot applications
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)
Type of mounting	Screwed tightly Can be inserted in slot lengthwise
Mounting position	Any
Product weight	9 g
Housing material	PA-reinforced High-alloy stainless steel
Material of union nut	Brass, nickel-plated
Switching status indication	LED yellow
Status indicator	LED red
Setting options	IO-Link® Capacitive pushbutton
Ambient temperature with flexible cable installation	-20 °C...70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1