


Servo motor

EMMH-AS-108-MA-HS-S1MB-T

Part number: 8215359

FESTO



Data sheet

Feature	Value
Ambient temperature	-30 °C...40 °C
Note on ambient temperature	Up to 80°C with derating -2%/°C
Max. installation height	3000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 100%
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	F
Max. winding temperature	155 °C
Rating class as per EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM B14 IM V18
Mounting position	optional
Degree of protection	IP69K
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime under nominal conditions	20000 h
Interface code, motor out	108C
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M17x0.75
Electrical connection 1, number of connections/cores	15
Pollution degree	2
Note on materials	RoHS-compliant
Corrosion resistance class CRC	4 - Very high corrosion stress (except laser marking)
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	Approved for direct contact with food
Vibration resistance	As per EN 60068-2-6

Feature	Value
Shock resistance	As per EN 60068-2-29 15 g/11 ms to EN 60068-2-27
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Nominal operating voltage DC	680 V
Type of winding switch	Star inside
Number of pole pairs	5
Standstill torque	5.9 Nm
Nominal torque	3.85 Nm
Peak torque	19 Nm
Nominal rotary speed	2000 rpm
Max. rotational speed	7000 rpm
Max. mechanical speed	7000 rpm
Angular acceleration	100000 rad/s ²
Nominal power rating of motor	810 W
Continuous stall current	6.5 A
Nominal motor current	4.4 A
Peak current	22.8 A
Motor constant	0.89 Nm/A
Standstill torque constant	0.92 Nm/A
Voltage constant, phase-to-phase	59.5 mV/min
Phase-phase winding resistance	1.03 Ohm
Phase-phase winding inductance	5.3 mH
Winding longitudinal inductivity Ld (phase)	2.4 mH
Winding cross inductivity Lq (phase)	2.7 mH
Electric time constant	5.2 ms
Thermal time constant	82 min
Thermal resistance	0.77 K/W
Measuring flange	300 x 300 x 30 mm, steel
Mass moment of inertia of rotor	3.57 kgcm ²
Total mass moment of inertia of output	4.3 kgcm ²
Product weight	8900 g
Permissible axial shaft load	137 N
Permissible radial shaft load	685 N
Rotor position sensor	Absolute multi-turn encoder
rotor position sensor, manufacturer designation	EQI 1331
rotor position sensor, absolute detectable revolutions	4096
Rotor position encoder interface	EnDat® 22
Rotor position sensor, encoder measuring principle	Inductive
rotor position sensor, DC operating voltage	5 V
rotor position sensor, DC operating voltage range	3.6 V...14 V
rotor position sensor, position values per revolution	524288
Rotor position transducer resolution	19 bit
rotor position sensor, system accuracy of angle measurement	-65 arcsec...65 arcsec
Brake holding torque	11 Nm
Operating voltage DC for brake	24 V
Brake current consumption	0.57 A
Power consumption, brake	13.6 W
Brake coil resistance	42.1 Ohm

Feature	Value
Brake coil inductivity	2600 mH
Brake separation time	60 ms
Brake closing time	58 ms
DC brake response delay	10 ms
Max. brake no-load speed	10000 rpm
Max. friction per braking process	910 J
Number of emergency stops per hour	1
Total brake friction	910 kJ
Mass moment of inertia of brake	0.73 kgcm ²
Switching cycles holding brake	10 million idle actuations (without friction work!)
Mean time to failure (MTTF), subcomponent	190 years, rotor position sensor