

Filter regulator MS4-LFR-1/4-D7-C-R-M-PAGN-AS-WR

Part number: 8229739

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | 4 |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Vertical +/-5° |
| Grade of filtration | 5 µm |
| Condensate drain | Manually rotating |
| Design | Filter regulator without pressure gauge |
| Max. condensate volume | 19 ml |
| Controller function | Output pressure constant With secondary venting With return flow function |
| Bowl guard | Plastic bowl guard |
| Degree of condensate separation | 75 % |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | Prepared for G1/4 |
| Operating pressure | 0.08 MPa...1.4 MPa 0.8 bar...14 bar |
| Pressure regulation range | 0.5 bar...12 bar |
| Max. pressure hysteresis | 0.025 MPa 0.25 bar 3.625 psi |
| Standard nominal flow rate (standardised to DIN 1343) | 1200 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:4:-] Inert gases |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C...60 °C |
| Suitable for use with food | See supplementary material information |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [6:4:4] |
| Media temperature | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Pore size | 5 µm |
| Product weight | 275 g |

| Feature | Value |
|------------------------------|---|
| Type of mounting | Either: Front panel mounting In-line installation With accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Note on materials | RoHS-compliant |
| Material sub-base | Die-cast aluminium |
| Material control panel | PA POM |
| Material seals | NBR |
| Material filter | PE |
| Material housing | Die-cast aluminium |
| Material membrane | NBR |
| Material bowl | PC |
| Material separating plate | POM |