

Servo motor EMMT-AS-80-S-HS-RMYB

Part number: 8160645

FESTO



Data sheet

Feature	Value
Ambient temperature	-15 °C...40 °C
Note on ambient temperature	Up to 80 °C with derating of -1.5% per degree Celsius
Max. installation height	4000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	F
Max. winding temperature	155 °C
Rating class according to EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type as per EN 60034-7	IM B5 IM V1 IM V3
Mounting position	Any
Degree of protection	IP40
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor shaft with rotary shaft seal IP67 for motor housing, incl. connection technology
Concentricity, coaxiality, axial runout according to DIN SPEC 42955	N
Balancing quality	G 2.5
Detent torque	<1,0% vom Spitzendrehmoment
Bearing lifetime, under nominal conditions	20000 h
Interface code, motor out	80P
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	15
Contamination level	2
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress

Feature	Value
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Certification	RCM compliance mark German Technical Control Board (TÜV) c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Certificate issuing authority	TÜV 968/INS 464.00/24 UL E342973
Nominal operating voltage DC	680 V
Type of winding switch	Star inside
Number of pole pairs	5
Stall torque	1.46 Nm
Nominal torque	1.3 Nm
Peak torque	2.8 Nm
Nominal rotary speed	3000 rpm
Max. rotational speed	8950 rpm
Angular acceleration	100000 rad/s ²
Motor nominal power	408 W
Continuous stall current	2 A
Motor nominal current	1.76 A
Peak current	5.4 A
Motor constants	0.74 Nm/A
Standstill torque constant	0.89 Nm/A
Voltage constant, phase-to-phase	53.6 mVmin
Phase-phase winding resistance	12.4 Ohm
Winding inductance phase-phase	39.8 mH
Winding longitudinal inductivity Ld (phase)	25 mH
Cross inductivity Lq (phase)	29.8 mH
Electric time constant	4.8 ms
Thermal time constant	42 min
Thermal resistance	0.95 K/W
Measuring flange	250 x 250 x 15 mm, steel
Total output inertia moment	0.897 kgcm ²
Product weight	2720 g
Permissible axial shaft load	120 N
Permissible radial shaft load	620 N
Rotor position sensor	Safety encoder, absolute multi-turn
Rotor position sensor for manufacturer designation	EQI 1131
Rotor position encoder for absolutely detectable revolutions	4096
Rotor position sensor interface	EnDat® 22
Rotor position sensor measuring principle	Inductive
Rotor position encoder for DC operating voltage	5 V
Rotor position encoder for DC operating voltage range	3.6 V...14 V
Rotor position encoder for positional values per revolution	524288
Rotor position sensor resolution	19 bit
Rotor position encoder system accuracy angle measurement	-120 arcsec...120 arcsec
Brake holding torque	4.5 Nm
Brake DC operating voltage	24 V

Feature	Value
Brake power consumption	12 W
	1 Safety device Safety integrity level 3 See user documentation Reliable recording and transmission of single-turn position data Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive Performance Level e, Category 3 See user documentation Reliable recording and transmission of single-turn position data Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive
Brake mass moment of inertia	0.249 kgcm ²
Switching cycles, holding brake	10 million idle actuations (without friction work!)
PFHd, subcomponent	15 x 10E-9, encoder
Duration of use Tm, subcomponent	20 years, rotor position sensor