


Stop kit DADP-SP-G9-10-F

Part number: 8173537

FESTO



Data sheet

Feature	Value
Size	10
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Max. stop force	100 N
Max. tightening torque	0.9 Nm
Tightening torque tolerance	± 15 %
Product weight	27 g
Type of mounting	Direct fastening via thread
Note on materials	RoHS-compliant
Stops material	High-alloy steel
Material of screws	Steel