


Adapter plate VABA-C13-G14

Part number: 8194539

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Adapter for remote application
Operating pressure	0 MPa...0.8 MPa 0 bar...8 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:7:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Temperature of medium	-40 °C...80 °C
Ambient temperature	-40 °C...80 °C
Product weight	222 g
Type of mounting	With accessories
Pneumatic connection	Sub-base design, airing
Pneumatic connection 1	G1/4
Pneumatic connection 2	G¼
Pneumatic connection 4	G1/4
Note on materials	RoHS-compliant
Cover material	Smooth-anodized wrought aluminum alloy (20 µm)
Seals material	EPDM NBR
Housing material	Smooth-anodized wrought aluminum alloy (20 µm)
Material of screws	High-alloy stainless steel