


Axial kit EAMM-A-S48-80PB

Part number: 8197487

FESTO



Data sheet

| Feature | Value |
|--------------------------|------------------------|
| Nominal length | 72 mm...72 mm |
| Mounting position | Any |
| Max. rotational speed | 6000 rpm...6000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...-25 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C...-10 °C |
| Mass moment of inertia | 34.8 kgmm ² |
| Transferable torque | 17 Nm |
| Product weight | 600 g...600 g |
| Interface code, actuator | S48 |
| Interface code, motor in | 80PB 80R |
| Note on materials | RoHS-compliant |