

Axial kit EAMM-A-C50-10-88C-S5

Part number: 8216589

FESTO



Data sheet

| Feature | Value |
|--------------------------|------------------------|
| Nominal length | 62 mm |
| Mounting position | Any |
| Gear ratio | 1:1 |
| Max. rotational speed | 6500 rpm |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 100 % |
| Degree of protection | IP69K |
| Ambient temperature | -10 °C...60 °C |
| Mass moment of inertia | 34.8 kgmm ² |
| Transferable torque | 17 Nm |
| Product weight | 1150 g |
| Interface code, actuator | C50-10 |
| Interface code, motor in | 88C |
| Note on materials | RoHS-compliant |