

Axial kit EAMM-A-L95-160G-G2

Part number: 8197453

FESTO



Data sheet

Feature	Value
Nominal length	112 mm...112 mm
Mounting position	Any
Max. rotational speed	4500 rpm...4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	430 kgmm ²
Transferable torque	200 Nm
Product weight	6264 g...6264 g
Interface code, actuator	L95
Interface code, motor in	160G
Note on materials	RoHS-compliant