

Filter regulator MS4-LFR-1/8-D7-C-R-M-PAGN-AS-WR

Part number: 8229778

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | 4 |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 5 µm |
| Condensate drain | Manually rotating |
| Structural design | Filter regulator without pressure gauge |
| Max. condensate volume | 19 ml |
| Controller function | Outlet pressure constant With secondary exhausting With return flow function |
| Bowl guard | Plastic bowl guard |
| Degree of condensate separation | 75 % |
| Pressure gauge | G1/4 prepared |
| Operating pressure | 0.08 MPa...1.4 MPa 0.8 bar...14 bar |
| Pressure regulation range | 0.5 bar...12 bar |
| Max. pressure hysteresis | 0.025 MPa 0.25 bar 3.625 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 850 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [-:4:-] Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C...60 °C |
| For use in the food industry | See supplementary material information |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:4:4] |
| Temperature of medium | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Pore size | 5 µm |
| Product weight | 275 g |

| Feature | Value |
|--------------------------------|--|
| Type of mounting | Optionally: Front panel mounting Line installation With accessories |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | G1/8 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast aluminum |
| Material of operator panel | PA POM |
| Seals material | NBR |
| Compressed air filter material | PE |
| Housing material | Die-cast aluminum |
| Diaphragm material | NBR |
| Material of bowl | PC |
| Separating disc material | POM |