


Axial kit EAMM-A-S38-55A-G3

Part number: 8197483

FESTO



Data sheet

Feature	Value
Nominal length	47 mm...47 mm
Mounting position	Any
Max. rotational speed	8000 rpm...8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	260 g...260 g
Interface code, actuator	S38
Interface code, motor in	55A
Note on materials	RoHS-compliant