

Axial kit EAMM-A-C68-16-114CC-S5

Part number: 8230191

FESTO



Data sheet

Feature	Value
Nominal length	78.2 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	6500 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100 %
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	21 Nm
Product weight	2160 g
Interface code, actuator	C68-16
Interface code, motor in	114CC
Note on materials	RoHS-compliant