


Axial kit EAMM-A-D50-60G-G2

FESTO

Part number: 8197498



Data sheet

Feature	Value
Nominal length	77.5 mm...77.5 mm
Mounting position	Any
Max. rotational speed	6000 rpm...6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...-25 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...-10 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	21 Nm
Product weight	950 g...950 g
Interface code, actuator	D50
Interface code, motor in	60G
Note on materials	RoHS-compliant