



Variklio kabelis NEBM-H6G4-E-7.5-Q13N-LE4

Gaminio numeris: 5219199

★ Kernprogramm

FESTO



Tech. Duomenys

Savybės	Reikšmė
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	Connection pattern H6, coded for the motor
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Nominalus DC įtampos lygis	0 ... 300 V
Nominalus AC įtampos lygis	0 ... 300 V
Leistina srovės apkrova prie 40°C	9,5 A
Atsparumas smūgiams	2 kV
Kabelio ilgis	7,5 m
Kabelio priedas	Suitable for energy chains
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	≥ 55 mm
Bending radius, flexible cable installation	≥ 55 mm
Kabelio skersmuo	7,3 mm
Kabelio struktūra	4x0,79
Nominalus laidininko skerspjūvis	0,79 mm ²
Nominal conductor cross section (AWG)	AWG18
Laido galai	Laido antgalis
Apsaugos klasė	IP20
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 90 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-25 ... 90 °C
CE ženklas (žr. deklaraciją)	atitinka EU reikalavimus žemose įtampose in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	0 - No corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	Juodas
Material housing	PA
Korpuso spalva	baltas
Material insulation	PVC