


Vod utičnice KMEB-1-230AC-5

Broj artikla: 151691

FESTO

predugrađeno, za MEBH, MOEBH ventile i N2 elektromagnete.



Tehnički podaci

Svojstvo	Vrednost
Položaj ugradnje	proizvoljno
Težina proizvoda	230 g
Električni priključak 1	Utičnica, to EN 175301-803, Tip C
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, note about the cable outlet	90°
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	na elektromagnetnom ventilu sa središnjim vijkom M2,5
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	3
Nazivni pogonski napon AC	230 V
Čvrstoća na udarno naprezanje	4 kV
Priključak uzemljenja	postoji
Dužina kabla	5 m
Svojstvo kabla	Standard
Prečnik kabla	5,2 mm
Struktura kabla	3x0,5
Krajevi žica	Završetak žice
Mehanička zaštita	IP65 prema IEC 60529
Temperatura okoline	-20 ... 80 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material cable sheath	PVC
Material housing	PA66-GF30
Material seals	NBR
Material electrical contact	Silver-plated copper alloy