



Utikač SEA-3GS-M8-S

Broj artikla: 192009

FESTO

za ventilske blokove.



Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	EN 61076-2-104 EN 61984
Položaj ugradnje	proizvoljno
Težina proizvoda	6 g
Veličina kontejnera	1
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock with hexagon A/F 9 mm and longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, connection technology	Vijčana stezaljka
Electrical connection 2, number of pins/wires	8
Područje pogonskog napona DC	≤ 60 V
Područje pogonskog napona AC	≤ 60 V
Strujna opteretivost kod 40°C	3 A
Čvrstoća na udarno naprezanje	1,5 kV
Navojni spoj kabla	Pg7
Prečnik kabla	2,5 ... 5 mm
Nazivni presek provodnika	0,14 ... 0,5 mm ²
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline	-40 ... 85 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-niski napon-smernica
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	1 - Low corrosion stress
Material housing	PA
Boja kućišta	crno
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Brass, gold-plated