

Plastično crevo PFAN-6X1-NT

Broj artikla: 197062

FESTO

dozvoljeno u prehrambenom području, za temperature do 150°C..



Tehnički podaci

| Svojstvo | Vrednost |
|---|--|
| Spoljašnji prečnik | 6 mm |
| Radius savijanja, merodavan za protok | 50 mm |
| Unutrašnji prečnik | 4 mm |
| Min. radius savijanja | 12 mm |
| Uputstva za korišćenje | Tubing without printing |
| Operating pressure for entire temperature range | -0,095 ... 0,7 MPa |
| Pogonski pritisak kompletnog temperaturnog područja | -0,95 ... 7 bar |
| Operating pressure for entire temperature range | -13,775 ... 101,5 psi |
| Temperature-dependent operating pressure | -0,095 ... 1,6 MPa |
| Pogonski pritisak zavisao od temperature | -0,95 ... 16 bar |
| Temperature-dependent operating pressure | -13,775 ... 232 psi |
| Napomena za pogonski pritisak | Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi |
| Pogonski medijum | Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour |
| Material fire test | UL94 V-0 |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Food-safe | See Supplementary material information See declaration of conformity |
| Note on temperature of medium | Water vapour: max. 120°C |
| Temperatura okoline | -20 ... 150 °C |
| Težina proizvoda prema dužini | 0,034 kg/m |
| Pneumatski priključak | For push-in connector outside diameter 6 mm za spajanje navlačenjem, unutrašnji prečnik 4 mm sa maticom for barbed connector internal diameter 4 mm |
| Boja | prirodno |
| Tvrdoća po Shoreu | D 60 +5 |
| Materijal - napomena | RoHS komformnost |
| Material tubing | PFA |