

# Plastično crevo PFAN-12X1,75-NT

Broj artikla: 197065

FESTO

dozvoljeno u prehrambenom području, za temperature do 150°C..



## Tehnički podaci

Svojstvo	Vrednost
Spoljašnji prečnik	12 mm
Radius savijanja, merodavan za protok	165 mm
Unutrašnji prečnik	8,4 mm
Min. radius savijanja	29 mm
Uputstva za korišćenje	Tubing without printing
Operating pressure for entire temperature range	-0,095 ... 0,7 MPa
Pogonski pritisak kompletnog temperaturnog područja	-0,95 ... 7 bar
Operating pressure for entire temperature range	-13,775 ... 101,5 psi
Temperature-dependent operating pressure	-0,095 ... 1,6 MPa
Pogonski pritisak zavisao od temperature	-0,95 ... 16 bar
Temperature-dependent operating pressure	-13,775 ... 232 psi
Napomena za pogonski pritisak	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
Pogonski medijum	Kompresovani vazduh prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information See declaration of conformity
Note on temperature of medium	Water vapour: max. 120°C
Temperatura okoline	-20 ... 150 °C
Težina proizvoda prema dužini	0,125 kg/m
Pneumatski priključak	For push-in connector outside diameter 12 mm
Boja	prirodno
Tvrdoća po Shoreu	D 60 +5
Materijal - napomena	RoHS komfornost
Material tubing	PFA