

Parallel kit EAMM-U-110-C80-19-108C-120-S5

Part number: 8216604

FESTO



Data sheet

Feature	Value
Size	110
Mounting position	Any
Gear ratio	1:1
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 100 %
Degree of protection	IP69K
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	794.1 kgmm ²
Transferable torque	25 Nm
Product weight	7200 g
Interface code, actuator	C80-19
Interface code, motor in	108C
Note on materials	RoHS-compliant