

# Priključni kabl KMP6-15P-12-10



Broj artikla: 527545

Classic - nicht für Neukonstruktionen verwenden

za ventilski blok CPV-SC, sa Sub-D utikačem 15-polnim, 10 m dug.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Odgovara standardu	DIN 41652
Cable identification	Without inscription label holder
Frekvencija priključivanja	50
Težina proizvoda	1.134 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	15
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	15
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Strujna opteretivost kod 40°C	2,8 A
Čvrstoća na udarno naprezanje	1 kV
Dužina kabla	10 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 86 mm
Bending radius, flexible cable installation	≥ 129 mm
Prečnik kabla	8,6 mm
Odstupanje prečnika kabla	± 0,25 mm
Struktura kabla	15x0,34
Nazivni presek provodnika	0,34 mm <sup>2</sup>
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP40
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 70 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
Temperatura ležaja	-20 ... 75 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komfornost
Stepen zagađenja	2
Material cable sheath	PVC

Svojstvo	Vrednost
Boja izolacije	sivo
Material housing	PBT ojačan
Boja kućišta	sivo
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy