



Spojni vod VMPA-KMS1-8-5

Broj artikla: 533196

FESTO

za multipol priključak na ventilski blok MPA-S.



Tehnički podaci

Svojstvo	Vrednost
Zasnovano na normi	DIN 41652
Cable identification	sa priborom
Frekvencija priključivanja	50
Težina proizvoda	510 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, occupied pins/wires	9
Electrical connection 1, type of mounting	3x M3 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	10
Electrical connection 2, occupied pins/wires	9
Područje pogonskog napona DC	0 ... 30 V
Nazivni pogonski napon DC	24 V
Dozvoljeno strujno opterećenje	3 A
Čvrstoća na udarno naprezanje	1 kV
Dužina kabla	5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	28,6 mm
Bending radius, flexible cable installation	71,5 mm
Navojni spoj kabla	M20x1,5
Prečnik kabela	7,15 mm
Odstupanje prečnika kabla	± 0,3 mm
Struktura kabla	10x0,34
Nazivni presek provodnika	0,34 mm ²
Krajevi žica	Cut off bluntly
Mehanička zaštita	IP65 prema IEC 60529
Note on degree of protection	u montiranom stanju
Temperatura okoline	-25 ... 80 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 70 °C
CE znak (vidi izjavu o usklađenosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS komformnost
Stepen zagađenja	3
Klasa korozione otpornosti KBK	2 - Moderate corrosion stress
Material cable sheath	PVC

Svojstvo	Vrednost
Boja izolacije	sivo
Material housing	PA
Boja kućišta	sivo
Material of union nut	PA
Material seals	CR NBR
Material electrical contact	Gold-plated copper alloy